# Product Bulletin: Stainless Steel Manifolds

## Watts Radiant

3131 W. Chestnut Expressway

## Our new Stainless Steel manifolds offer several great features:

- \* Flexible, modular and singular design system
- \* Easy-to-assemble construction
- \* Precise flow control and balancing
- \* Fittings for both PEX and Onix radiant tubing
- \* Control for hydronic floor heating, fan coil heating, or baseboard heating
- \* No sealant, no teflon

Stainless Steel manifolds are sold in 1 to 12-branch pairs for easy assembly in the field. They are 1" AISI 304 Stainless Steel and can handle up to 12 gpm. Manifold sections are easily connected together, if more circuits are required. Simply thread two sections together with the use of 1" manifold coupling and tighten. Make sure the gasket is installed prior to assembly.

#### **Manifolds Are Sold In Pairs:**

- 1) Balancing Valve Manifold (with optional Actuator)
- 2) Flow Indicator Manifold

#### Accessories

Accessories include Vent/Purge Assembly, Valve Actuator, Transitional Fittings, Mounting Brackets (*standard with manifold pairs*), and Lockable Manifold Boxes (Vent/Purge, End Caps, Trunk Isolation Valves and Transition Fittings all have flat gaskets that must be installed without the use of sealants or teflon.)

#### Flow Balancing

Balancing is achieved by either:

- 1. Adjusting the Balancing Knob, or
- Adjusting the dial located under the Adjustment Cap. Dial is adjusted with the use of the Adjustment Key. The key comes attached to the manifold via nylon tie.

Flow can be visually fine-tuned by viewing the sight glass indicator while adjusting the balancing valve on the return manifold.

#### **On-Off Circuit Control**

For systems requiring individual circuit thermostatic control, an electronic Valve Actuator is installed. Valve Actuators are four-wire, to connect to the zone thermostat and use end switch wires to activate the circulator. With this arrangement, every room can be thermostatically controlled from one central distribution manifold.

#### Note:

Depending on the actuator style used, some circuit adjustment may be necessary.

Additional flow control can be achieved by installing individual circuit isolation mini-ball valves. These valves allow for balancing and shut-off capabilities without having to remove the adjustment cap or thermal actuator.

#### Note:

- 1) Stainless Steel Manifolds can be used to control fan coils or baseboard units, as well as floor heating.
- Manifolds are not intended to exceed 87 psi at 194°F operating conditions.



ITEM NUMBER	DESCRIPTION	LIST PRICE
D3804000SS	M1 Stainless Steel Manifold Pair with Flow Meters	\$144.00
D3803002SS	M2 Stainless Steel Manifold Pair with Flow Meters	\$178.00
D3803003SS	M3 Stainless Steel Manifold Pair with Flow Meters	\$225.75
D3803004SS	M4 Stainless Steel Manifold Pair with Flow Meters	\$273.00
D3803005SS	M5 Stainless Steel Manifold Pair with Flow Meters	\$355.00
D3803006SS	M6 Stainless Steel Manifold Pair with Flow Meters	\$383.25
D3803007SS	M7 Stainless Steel Manifold Pair with Flow Meters	\$427.00
D3803008SS	M8 Stainless Steel Manifold Pair with Flow Meters	\$472.50
D3803009SS	M9 Stainless Steel Manifold Pair with Flow Meters	\$522.00
D3803010SS	M10 Stainless Steel Manifold Pair with Flow Meters	\$ \$572.25
D3803011SS	M11 Stainless Steel Manifold Pair with Flow Meters	\$ \$624.00
D3803012SS	M12 Stainless Steel Manifold Pair with Flow Meters	\$ \$677.25
D4201720-N	Trunk Isolation Ball Valve with Temperature Gauge	\$48.90
D4201715-N	Vent and Purge Assembly	\$35.70
D063064-N	Manifold End Cap	\$6.06
D4201480-N	BSP to NPT Transition Fitting	\$31.50
D402178-N	1" x 1" Manifold Coupling	\$20.88
D4201480-N	Circuit Isolation Plug	\$9.36
D4201710-N	Circuit Isolation Mini Ball Valve	\$23.10
PZ656104	Valve Actuator	\$63.00
Note:		
- Order T-20 Compressi	on PEX fittings or Onix fittings and clamps separately.	
- Stainless Steel manifo	lds can be ordered fully-assembled with all optional components	s for 15%
above the cost of all c	omponents	

- (Vent/Purge, End Caps, Trunk Isolation Valves and Transition Fittings all have flat gaskets that must be installed without the use of sealants or teflon.)

### Product Bulletin: Stainless Steel Manifolds Available at: 631-240-9173

PEXHEAT.COM



3131 W. Chestnut Expressway Springfield, MO 65802 ph: 417.864.6108 fax: 417.864.8161 www.wattsradiant.com



the insert fitting - see diagram above).